




Tag RFID

ID-TAG/30X2.5/06 - 896 bit



Aplikasi

Suhu pengoperasian (aktif)	[°C]	-40...85
Suhu puncak (pasif)	[°C]	90

Data kelistrikan

Frekuensi pengoperasian	[MHz]	13,56
Ukuran memori	[bit]	896
Tipe memori		EEPROM
Tipe chip		ICODE SLIX
Jumlah blok		28
Ukuran blok	[Byte]	4
Nomor Identifikasi Unik (UID)	[Byte]	8
Standar RFID		ISO 15693
Siklus pembacaan maks.		tidak terbatas
Siklus penulisan maks.		100000

Kondisi pengoperasian

Suhu sekitar	[°C]	-40...85
Suhu penyimpanan	[°C]	-40...90
Perlindungan		IP 68; IP 69K

Pengujian/persetujuan

Tahan guncangan	DIN IEC 68-2-27	40 g 18 ms
Ketahanan terhadap getaran	DIN IEC 68-2-6	10 g 10...2000 Hz
Persetujuan radio		ISO 15693

Data teknis

Berat	[g]	4.75
Tipe pemasangan		pemasangan pada bahan non-logam; (pengencangan sekrup ; menempel pada permukaan)
Dimensi	[mm]	Ø 30 / L = 3
Material		PA 6 hitam

Keterangan

Jumlah paket		1 buah
--------------	--	--------



Tag RFID

ID-TAG/30X2.5/06 - 896 bit

Data lain

Jarak pembacaan ketika dipasang pada non-logam (mm)

ANT410 / DTI410	15
ANT411 / DTI411	20
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	15
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	40
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	30
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	50
ANT513 / DTI513 / DTC510	65
ANT515 / DTI515 / ANT516 / DTI516	35
ANT600 / DTI600	140