


DTE105



Unit evaluasi RFID LF/ HF

DTELF/HFABRWITUS00




Aplikasi		
Aplikasi		hingga 4 kepala baca/tulis tipe ANT41x/ANT51x
Data kelistrikan		
Tegangan pengoperasian	[V]	18...30 DC
Konsumsi arus	[mA]	< 3000
Input/output		
Jumlah input dan output		Jumlah output digital: 4
Output		
Jumlah output digital		4
Beban arus maks. per output	[mA]	500; (IO 1,2; IO 3,4: 1000 mA)
Interface		
Interface komunikasi		Ethernet
Ethernet - Internet of Things		
Standar transmisi		10Base-T; 100Base-TX
Laju transmisi		10 MBit/s; 100 MBit/s
Protokol		MQTT JSON
Tipe penggunaan		transmisi data; pengaturan parameter
Kondisi pengoperasian		
Suhu sekitar	[°C]	-20...60
Suhu penyimpanan	[°C]	-20...85
Perlindungan		IP 67



Unit evaluasi RFID LF/ HF

DTELF/HFABRWITUS00

Pengujian/persetujuan		
Tahan guncangan	IEC 60028-2-27	15 g 11 ms
Ketahanan terhadap getaran	IEC 60028-2-6	±1.6 mm (17...18 Hz) / 2 g (10...150 Hz)
Data teknis		
Berat	[g]	395.9
Dimensi	[mm]	115 x 46.2 x 85
Material	bagian atas: PA Grivory GV5H oranye; bagian atas: TPE; bagian bawah: GD-ALSi12	
Elemen display/pengoperasian		
Display	suplai tegangan	1 x LED, hijau
		1 x LED, kuning
	Ethernet TCP/IP	2 x LED, merah/hijau
	Ethernet	1 x LED, hijau
		1 x LED, kuning
	Input/output	1 x LED, hijau
		1 x LED, kuning
Aksesori		
Item dikirim	Tutup pelindung: M12, E73004	
Keterangan		
Jumlah paket	1 buah	
Koneksi listrik - Ethernet		
Konektor: 2 x M12; pengkodean: D		
		
Port 1/2		
1	TD+	
2	RD+	
3	TD-	
4	RD-	
Koneksi listrik - Koneksi proses		
Konektor: 4 x M12; pengkodean: A		
		




Unit evaluasi RFID LF/ HF

DTELF/HFABRWITUS00

IO 1...4	
1	L+
2	IN (I/Q)
3	L-
4	OUT (C/Qo); IN (C/Qi)
5	n.c.

Koneksi listrik - suplai tegangan

Konektor: 1 x M12; pengkodean: A



AUX	
1	24 V DC
2	n.c.
3	0 V
4	n.c.
5	n.c.