




Tag RFID

ID-TAG/30X2,8/03 - 64 Kbit



Aplikasi		
Suhu pengoperasian (aktif)	[°C]	-25...85
Suhu puncak (pasif)	[°C]	90
Data kelistrikan		
Frekuensi pengoperasian	[MHz]	13,56
Ukuran memori	[bit]	65536
Tipe memori		FRAM
Tipe chip		MB89R112
Jumlah blok		256
Ukuran blok	[Byte]	32
Nomor Identifikasi Unik (UID)	[Byte]	8
Standar RFID		ISO 15693
Siklus pembacaan maks.		tidak terbatas
Siklus penulisan maks.		tidak terbatas
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...85
Suhu penyimpanan	[°C]	-40...90
Perlindungan		IP 68; IP 69K
Pengujian/persetujuan		
Persetujuan radio		ISO 15693
Data teknis		
Berat	[g]	3.85
Tipe pemasangan		pemasangan pada bahan non-logam; (pengencangan sekrup ; menempel pada permukaan)
Dimensi	[mm]	Ø 30 / L = 3
Material		PPA [ISO 1874: PA6T/6I-GF50]
Keterangan		
Jumlah paket		1 buah



Tag RFID

ID-TAG/30X2,8/03 - 64 Kbit

Data lain

Jarak pembacaan ketika dipasang pada non-logam (mm)

ANT410 / DTI410	15
ANT411 / DTI411	20
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	10
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	30
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	25
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	40
ANT513 / DTI513 / DTC510	65
ANT515 / DTI515 / ANT516 / DTI516	30
ANT600 / DTI600	115