




Tag RFID

ID-TAG/D4X22/03 - 2528 bit



Aplikasi		
Aplikasi	pengkodean carrier benda kerja pada konveyor perutean	
Suhu pengoperasian (aktif)	[°C]	-20...85
Suhu puncak (pasif)	[°C]	90
Data kelistrikan		
Frekuensi pengoperasian	[MHz]	13,56
Ukuran memori	[bit]	896
Tipe memori		EEPROM
Tipe chip		ICODE SLIX
Jumlah blok		28
Ukuran blok	[Byte]	4
Nomor Identifikasi Unik (UID)	[Byte]	8
Standar RFID		ISO 15693
Siklus pembacaan maks.		tidak terbatas
Siklus penulisan maks.		100000
Kondisi pengoperasian		
Suhu sekitar	[°C]	-20...85
Suhu penyimpanan	[°C]	-40...90
Perlindungan		IP 68
Pengujian/persetujuan		
Tahan guncangan	DIN IEC 68-2-27	40 g 18 ms
Ketahanan terhadap getaran	DIN IEC 68-2-6	10 g 10...2000 Hz
Persetujuan radio	ISO 15693	
Data teknis		
Berat	[g]	1.85
Tipe pemasangan	pemasangan pada bahan non-logam; (menempel pada permukaan)	
Dimensi	[mm]	Ø 4 / L = 22
Material	kaca	
Keterangan		
Jumlah paket	10 buah	



Tag RFID

ID-TAG/D4X22/03 - 2528 bit

Data lain

Jarak pembacaan ketika dipasang pada non-logam (mm)

ANT410 / DTI410	5
ANT411 / DTI411	10
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	5
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	20
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	15
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	30
ANT513 / DTI513 / DTC510	40
ANT515 / DTI515 / ANT516 / DTI516	10
ANT600 / DTI600	-