


DV1002



Strip LED RGBW

LED-Stripe-RGBW-500mm-IP68



Aplikasi		
Aplikasi		pensinyalan kondisi mesin
Data kelistrikan		
Tegangan pengoperasian	[V]	21.4...26.4 DC
Tegangan nominal DC	[V]	24; (sesuai SELV/PELV)
Konsumsi arus	[mA]	800
Suhu warna	[K]	4000
Fluks cahaya	[lm]	merah: 101.2; hijau: 188.8; biru: 37; putih: 285.2
Catatan tentang fluks cahaya	[lm]	indikasi fluks cahaya mengacu pada satu meter strip LED
Tipe masa pakai	[h]	30000
Input		
Sirkuit input dari input digital		24 V PNP
Kondisi pengoperasian		
Suhu sekitar	[°C]	-20...45
Kelembapan udara relatif maks.	[%]	90
Ketinggian maks. di atas permukaan laut	[m]	4000
Perlindungan		IP 68
Tingkat kekotoran		2
Pengujian/persetujuan		
Persetujuan		IEC 62471; IEC 62031
Data teknis		
Berat	[g]	72.4
Dimensi	[mm]	515 x 14.2 x 4.5
Material		TPU

DV1002



Strip LED RGBW

LED-Stripe-RGBW-500mm-IP68

Elemen display/pengoperasian		
Display	pensinyalan kondisi mesin	LED, multi-warna RGB
	lampu pemasangan	LED, putih

Keterangan	
Jumlah paket	1 buah

Koneksi listrik

Kabel: 0.3 m

Konektor: M12; pengkodean: A



1	+ merah
2	+ hijau
3	GND
4	+ putih
5	+ biru

Diagram dan grafik

