


DV1004



Strip LED RGBW

LED-Stripe-RGBW-1000mm-IP68



Aplikasi		
Aplikasi	pensinyalan kondisi mesin	
Data kelistrikan		
Tegangan pengoperasian	[V]	21.6...26.4 DC
Tegangan nominal DC	[V]	24; (sesuai SELV/PELV)
Konsumsi arus	[mA]	1600
Suhu warna	[K]	4000
Fluks cahaya	[lm]	merah: 101.2; hijau: 188.8; biru: 37; putih: 285.2
Catatan tentang fluks cahaya	[lm]	indikasi fluks cahaya mengacu pada satu meter strip LED
Tipe masa pakai	[h]	30000
Input		
Sirkuit input dari input digital	24 V PNP	
Kondisi pengoperasian		
Suhu sekitar	[°C]	-20...45
Kelembapan udara relatif maks.	[%]	90
Ketinggian maks. di atas permukaan laut	[m]	4000
Perlindungan		IP 68
Tingkat kekotoran		2
Pengujian/persetujuan		
Persetujuan	IEC 62471; IEC 62031	
Data teknis		
Berat	[g]	123.8
Dimensi	[mm]	1015 x 14.2 x 4.5
Elemen display/pengoperasian		
Display	pensinyalan kondisi mesin	LED, multi-warna RGB
	lampu pemasangan	LED, putih

Strip LED RGBW

LED-Stripe-RGBW-1000mm-IP68

Keterangan


Jumlah paket

1 buah

Koneksi listrik

Kabel: 0.3 m

Konektor: M12; pengkodean: A



- | | |
|---|---------|
| 1 | + merah |
| 2 | + hijau |
| 3 | GND |
| 4 | + putih |
| 5 | + biru |

Diagram dan grafik