




Tag RFID

ID-TAG/Tear Shape/06



Aplikasi

Aplikasi	pengkodean carrier benda kerja pada konveyor perutean	
Suhu pengoperasian (aktif) [°C]	-25...55	
Suhu puncak (pasif) [°C]	75	

Data kelistrikan

Frekuensi pengoperasian [MHz]	13,56	
Ukuran memori [bit]	896	
Tipe memori	EEPROM	
Tipe chip	ICODE SLIX	
Jumlah blok	28	
Ukuran blok [Byte]	4	
Nomor Identifikasi Unik (UID) [Byte]	8	
Standar RFID	ISO 15693	
Siklus pembacaan maks.	tidak terbatas	
Siklus penulisan maks.	100000	

Kondisi pengoperasian

Suhu sekitar [°C]	-25...55	
Suhu penyimpanan [°C]	-25...75	
Perlindungan	IP 66	

Pengujian/persetujuan

Tahan guncangan	DIN IEC 68-2-27	40 g 18 ms
Ketahanan terhadap getaran	DIN IEC 68-2-6	10 g 10...2000 Hz
Persetujuan radio	ISO 15693	

Data teknis

Berat [g]	21.6	
Tipe pemasangan	pemasangan pada bahan non-logam; (ring pengait)	
Dimensi [mm]	40 x 31 x 4.8	
Material	ABS	

Keterangan

Jumlah paket	5 buah	
--------------	--------	--



Tag RFID

ID-TAG/Tear Shape/06

Data lain

Jarak pembacaan ketika dipasang pada non-logam (mm)

ANT410 / DTI410	10
ANT411 / DTI411	20
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	15
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	40
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	30
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	45
ANT513 / DTI513 / DTC510	60
ANT515 / DTI515 / ANT516 / DTI516	30
ANT600 / DTI600	80