

DX2041



Display multifungsi untuk memantau sinyal standar analog

DISPLAY/AX460/AC/DC



potongan panel 91 x 43 mm



Karakteristik produk

Dimensi	[mm]	48 x 112 x 116
---------	------	----------------

Aplikasi

Aplikasi	menampilkan dan memantau sinyal analog; misalnya sensor tekanan, sensor suhu atau sensor aliran
----------	---

Data kelistrikan

Frekuensi AC	[Hz]	50...60
Tegangan pengoperasian	[V]	115...230 AC / 18...30 DC
Konsumsi arus	[mA]	100

Input/output

Jumlah input dan output	Jumlah input analog: 2
-------------------------	------------------------

Input

Jumlah input analog	2; (Spannungs- oder Stromeingang)	
Input analog (arus)	[mA]	0...20
Input analog (tegangan)	[V]	-10...10
Resolusi input analog	16 bit	
Input analog presisi	[%]	0,1

Kondisi pengoperasian

Suhu sekitar	[°C]	-20...60
Suhu penyimpanan	[°C]	-25...70
Perlindungan		IP 65
Terminal peringkat perlindungan		IP 20

Pengujian/persetujuan

EME	EN 61000-6-2
	EN 61000-6-3
	EN 61000-6-4

Data teknis

Berat	[g]	351
-------	-----	-----

DX2041



Display multifungsi untuk memantau sinyal standar analog

DISPLAY/AX460/AC/DC	
Tipe pemasangan	potongan panel: 91 x 43 mm
Dimensi [mm]	48 x 112 x 116
Material	Noryl UL94-V-0


Elemen display/pengoperasian

Display	display berwarna	display LCD grafis penuh, layar sentuh
---------	------------------	--

Koneksi listrik

terminal sekrup:

Koneksi



NC tidak digunakan