


E80394



Tag RFID

ID-TAG/174x70x17.6/04



Aplikasi

Aplikasi

Pengkodean RFID pada tangki logam

Data kelistrikan

Frekuensi pengoperasian [MHz]	860...930; (India: 865...867 MHz)
Ukuran memori [bit]	512
Tipe memori	EEPROM
Tipe chip	Impinj Monza 4QT
ID tag (TID) [Byte]	64
Kode produk elektronik (EPC)	96 bit; (bisa diperluas: 128 Bits)
Standar RFID	EPC Class1 GEN2/ISO 18000-6C
Siklus pembacaan maks.	tidak terbatas
Siklus penulisan maks.	100000

Kondisi pengoperasian

Suhu sekitar [°C]	-40...85
Suhu penyimpanan [°C]	-40...100
Perlindungan	IP 68

Data teknis

Berat [g]	129.4
Dimensi [mm]	70 x 174 x 17.6
Material	casing: polikarbonat-ABS

Keterangan

Jumlah paket	1 buah
--------------	--------

E80394



Tag RFID

ID-TAG/174x70x17.6/04

Data lain

jarak pembacaan (m)

DTE80x	3
DTE90x	3.3
ANT860 / ANT960	9
ANT820 / ANT920	2