




Antena kombinasi untuk navigasi dan radio

LTE/GNSS/FAKRA-Antenna



Data kelistrikan		
Konsumsi arus	[mA]	< 24
Interface		
GNSS		
Pita frekuensi	GPS: 1563...1587 MHz (L1); Galileo: 1559...1591 MHz (E1); Beidou: 1559...1591 MHz (B1C); GLONASS: 1593...1610 MHz (G1)	
Catatan tentang interface	Tegangan pengoperasian: 3...5,5 V DC	
	Impedansi: 50 Ohm	
	Polarisasi: RHCP	
	vertikal	
	LNA: 27 ± 1 dB	
	Rauschzahl: 2.2 dB	
Jaringan seluler		
Pita frekuensi	698 ...960 MHz; 710...2170 MHz; 2300...2690 MHz	
Catatan tentang interface	Impedansi: 50 Ohm	
	Polarisasi: linier vertikal	
Kondisi pengoperasian		
Suhu sekitar	[°C]	-40...85
Perlindungan		IP 6K6
Data teknis		
Berat	[g]	366
Tipe pemasangan		Gewinde

EC3158



Antena kombinasi untuk navigasi dan radio

LTE/GNSS/FAKRA-Antenna

Dimensi	[mm]	80 x 124 x 31
Material		PC hitam
Torsi pengencangan	[Nm]	< 5

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik - GPS

Kabel: 3 m
Konektor: 1 x FAKRA

Koneksi listrik - GSM

Kabel: 3 m
Konektor: 1 x FAKRA