




Tag RFID

ID-TAG/7.5X1.0/06



Aplikasi

Suhu pengoperasian (aktif) [°C]	-40...85
Suhu puncak (pasif) [°C]	85

Data kelistrikan

Frekuensi pengoperasian [MHz]	13,56
Ukuran memori [bit]	896
Tipe chip	ICODE SLIX
Jumlah blok	28
Ukuran blok [Byte]	4
Nomor Identifikasi Unik (UID) [Byte]	8
Standar RFID	ISO 15693

Kondisi pengoperasian

Suhu sekitar [°C]	-40...85
Suhu penyimpanan [°C]	-40...85
Perlindungan	IP 68

Pengujian/persetujuan

Tahan guncangan	DIN IEC 68-2-27	40 g (18 ms)
Ketahanan terhadap getaran	DIN IEC 68-2-6	10 g (10...2000 Hz)

Data teknis

Berat [g]	2.1
Dimensi [mm]	Ø 7.5 / L = 1
Material	casing: Epoxydharz

Keterangan

Jumlah paket	10 buah
--------------	---------



Tag RFID

ID-TAG/7.5X1.0/06

Data lain

Jarak pembacaan ketika dipasang pada non-logam (mm)

ANT410 / DTI410	10
ANT411 / DTI411	10
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	10
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	20
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	15
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	25
ANT513 / DTI513 / DTC510	30
ANT515 / DTI515 / ANT516 / DTI516	10
ANT600 / DTI600	-