




Tag RFID

ID-TAG/16X3/06



Aplikasi

Aplikasi	pengkodean carrier benda kerja pada konveyor perutean	
Suhu pengoperasian (aktif) [°C]		-25...85
Suhu puncak (pasif) [°C]		85

Data kelistrikan

Frekuensi pengoperasian [MHz]		13,56
Ukuran memori [bit]		896
Tipe memori		EEPROM
Tipe chip		ICODE SLIX
Jumlah blok		28
Ukuran blok [Byte]		4
Nomor Identifikasi Unik (UID) [Byte]		8
Standar RFID		ISO 15693
Siklus pembacaan maks.		tidak terbatas
Siklus penulisan maks.		100000

Kondisi pengoperasian

Suhu sekitar [°C]		-25...85
Suhu penyimpanan [°C]		-40...85
Perlindungan		IP 68

Pengujian/persetujuan

Tahan guncangan	DIN IEC 68-2-27	40 g 18 ms
Ketahanan terhadap getaran	DIN IEC 68-2-6	10 g 10...2000 Hz
Persetujuan radio		ISO 15693

Data teknis

Berat [g]		12.4
Tipe pemasangan	pemasangan pada bahan non-logam; (menempel pada permukaan)	
Dimensi [mm]		Ø 16 / L = 3
Material		PPS

Keterangan

Jumlah paket		10 buah
--------------	--	---------



Tag RFID

ID-TAG/16X3/06

Data lain

Jarak pembacaan ketika dipasang pada non-logam (mm)

ANT410 / DTI410	10
ANT411 / DTI411	15
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	10
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	25
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	20
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	35
ANT513 / DTI513 / DTC510	45
ANT515 / DTI515 / ANT516 / DTI516	20
ANT600 / DTI600	90