


Sensor area induktif

SIY-3120-ANKG

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	NPN
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	30...120
Casing	berbentuk silinder
Dimensi [mm]	Ø 164 / L = 63

Data kelistrikan

Tegangan pengoperasian [V]	12...36 DC
Konsumsi arus [mA]	< 7

Output

Desain kelistrikan	NPN
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	200
Frekuensi peralihan DC [Hz]	3

Zona pendeteksian

Jangkauan pendeteksian [mm]	30...120
-----------------------------	----------



Sensor area induktif

SIY-3120-ANKG

Jangkauan pendeteksian dapat disesuaikan	ya
Jangkauan pendeteksian pengaturan pabrik [mm]	120
Jangkauan pendeteksian real Sr [mm]	(30...120)

Akurasi/deviasi

Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2
Histeresis [X01]	< 15
Deviasi titik peralihan [X01]	-15...15

Kondisi pengoperasian

Suhu sekitar [°C]	-20...70
Perlindungan	IP 65

Pengujian/persetujuan

EME	EN 60947-5-2
-----	--------------

Data teknis

Casing	berbentuk silinder
Pemasangan	non-flush mountable
Dimensi [mm]	Ø 164 / L = 63
Material	casing: PBT; penutup bawah: aluminium

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
---------	------------------	-----------------

Aksesori

Item dikirim	sekrup: 1 x M16 x 90
--------------	----------------------


Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Kabel: 2 m, PVC; 3 x 0.5 mm ²
--

Koneksi



	Warna core :
BK =	hitam
BN =	coklat
BU =	biru