




Tag RFID

ID-TAG/Label 80X50/03 - 896 bit



Data kelistrikan

Frekuensi pengoperasian	[MHz]	13,56
Ukuran memori	[bit]	896
Tipe memori		EEPROM
Tipe chip		ICODE SLIX
Jumlah blok		28
Ukuran blok	[Byte]	4
Nomor Identifikasi Unik (UID)	[Byte]	8
Standar RFID		ISO 15693
Siklus pembacaan maks.		tidak terbatas
Siklus penulisan maks.		100000

Pengujian/persetujuan

Persetujuan radio	ISO 15693
-------------------	-----------

Data teknis

Berat	[g]	939.8
Tipe pemasangan		pemasangan pada bahan non-logam; (bisa merekat sendiri)
Dimensi	[mm]	50 x 80 x 0.1
Material		PP; perekat: HL2

Keterangan

Jumlah paket	500 buah
--------------	----------



Tag RFID

ID-TAG/Label 80X50/03 - 896 bit

Data lain

Jarak pembacaan ketika dipasang pada non-logam (mm)

ANT410 / DTI410	22
ANT411 / DTI411	35
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	20
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	65
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	50
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	85
ANT513 / DTI513 / DTC510	120
ANT515 / DTI515 / ANT516 / DTI516	50
ANT600 / DTI600	250