




Tag RFID

ID-TAG/4,35X3,6/03 - 896 bit



lubang pemasangan Ø 4.0 x 3.7 mm



Aplikasi

Instalasi	Pemasangan pada bahan logam dan non-logam
Suhu pengoperasian (aktif) [°C]	-40...85
Suhu puncak (pasif) [°C]	125

Data kelistrikan

Frekuensi pengoperasian [MHz]	13,56
Ukuran memori [bit]	896
Tipe memori	EEPROM
Tipe chip	ICODE SLIX
Jumlah blok	28
Ukuran blok [Byte]	4
Nomor Identifikasi Unik (UID) [Byte]	8
Standar RFID	ISO 15693
Siklus pembacaan maks.	tidak terbatas
Siklus penulisan maks.	100000

Kondisi pengoperasian

Suhu sekitar [°C]	-40...85
Suhu penyimpanan [°C]	-40...125
Perlindungan	IP 68

Pengujian/persetujuan

Persetujuan radio	ISO 15693
-------------------	-----------

Data teknis

Berat [g]	1.6
Tipe pemasangan	Pemasangan pada bahan logam dan non-logam
Dimensi [mm]	Ø 4.35 / L = 3.6
Material	PPA GF30; resin epoksi di dalam pot

Keterangan

Jumlah paket	10 buah
--------------	---------



Tag RFID

ID-TAG/4,35X3,6/03 - 896 bit

Data lain

Jarak pembacaan ketika dipasang pada non-logam (mm)

ANT410 / DTI410	4
ANT411 / DTI411	5
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	2
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	5
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	5
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	10
ANT513 / DTI513 / DTC510	10
ANT515 / DTI515 / ANT516 / DTI516	-
ANT600 / DTI600	-