


EVC950



Kabel koneksi

VDOAH050MSD0001C05STGH050MSS




Aplikasi		
Fitur khusus	Bebas halogen; Kontak berlapis emas; Kabel berpelindung; Kesesuaian rantai tarik	
Aplikasi	CAN bus	
Data kelistrikan		
Tegangan pengoperasian	[V]	< 30 AC / < 36 DC
Total beban arus maks.	[A]	4
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan	IP 67; IP 68; IP 69K	
Data teknis		
Berat	[g]	139.8
Dimensi	[mm]	14.5 x 14.5 x 48.5
Material bodi detakan	TPU	
Material mur	kuningan, berlapis nikel	
Material penyegel	FKM	
Kesesuaian rantai tarik	ya	
Kesesuaian rantai tarik	radius pembengkokan untuk penggunaan yang fleksibel	min. 10 x diameter kabel
	kecepatan pergerakan	maks. 3,3 m/dtk untuk panjang pergerakan horizontal 5 m dan akselerasi maks. 5 m/dtk²
	siklus pembengkokan	> 5 Mio.
	ketegangan torsional	± 180 °/m
Keterangan		
Jumlah paket	1 buah	

Kabel koneksi

VDOAH050MSD0001C05STGH050MSS

Koneksi listrik - colokan


Konektor: 1 x M12, lurus; pengkodean: A; Bodi cetakan: TPU, hitam; Penguncian: kuningan, berlapis nikel; Kontak: dilapisi emas;
Torsi pengencangan: 0.6...1.5 Nm



Koneksi listrik

Kabel: 1 m, PUR, Bebas halogen, ungu, Ø 8.4 mm, berpelindung; RD / BK: 2 x 0.75 mm² (42 x Ø 0.15 mm) + WH / BU: 2 x 0.5 mm² (19 x Ø 0.19 mm) + screen: 1 x 0.75 mm² (42 x Ø 0.15 mm)

Koneksi



Koneksi listrik - soket

Konektor: 1 x M12, bersiku; pengkodean: A; Bodi cetakan: TPU, hitam; Penguncian: kuningan, berlapis nikel; Segel: FKM; Kontak: dilapisi emas; Torsi pengencangan: 0.6...1.5 Nm

