

Sensor induktif

IAE3010-APKG



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya tertutup
Jangkauan pendeteksian [mm]	10
Casing	berbentuk silinder
Dimensi [mm]	Ø 20 / L = 92

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	15; (24 V)
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya tertutup
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	300
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian

Jangkauan pendeteksian [mm]	10
Jangkauan pendeteksian real Sr	10 ± 10 %
Jarak pengoperasian [mm]	0...8.1

Akurasi/deviasi

Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2
Histeresis [X01]	1...15



Sensor induktif

IAE3010-APKG

Deviasi titik peralihan	[X01]	-10...10
-------------------------	-------	----------

Kondisi pengoperasian

Suhu sekitar	[°C]	-25...80
Perlindungan		IP 65

Pengujian/persetujuan

EME	EN 60947-5-2	
MTTF	[ANN]	1076
Persetujuan UL	Ta	0...40 °C
	Tipe penutup	Type 1
	suplai tegangan	Hazardous voltage
	Nomor file UL	E174191

Data teknis

Berat	[g]	84
Casing		berbentuk silinder
Pemasangan		non-flush mountable
Dimensi	[mm]	Ø 20 / L = 92
Material		PBT; Jendela LED: PC

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
---------	------------------	-----------------

Aksesori

Item dikirim	Klem pemasangan: 1
--------------	--------------------

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

terminal: ...2.5 mm²; Selubung kabel: Ø 4.5...10 mm; Konektor kabel: M16 X 1.5

Koneksi

