


Sensor induktif

IB-3020-BPKG/55V



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	20
Casing	berbentuk silinder
Dimensi [mm]	Ø 34 / L = 82

Data kelistrikan

Tegangan pengoperasian [V]	10...55 DC
Konsumsi arus [mA]	5; (24 V)
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	60
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian

Jangkauan pendeteksian [mm]	20
Jangkauan pendeteksian real Sr	20 ± 10 %
Jarak pengoperasian [mm]	0...16.2

Akurasi/deviasi

Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2
Histeresis [X01]	1...15



Sensor induktif

IB-3020-BPKG/55V

Deviasi titik peralihan	[X01]	-10...10
-------------------------	-------	----------

Kondisi pengoperasian

Suhu sekitar	[°C]	-25...80
Perlindungan		IP 67

Pengujian/persetujuan

EME	EN 60947-5-2	
	EN 55011	kelas B
MTTF	[ANN]	1719

Data teknis

Berat	[g]	264
Casing		berbentuk silinder
Pemasangan		non-flush mountable
Dimensi	[mm]	Ø 34 / L = 82
Material		PBT

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
---------	------------------	-----------------

Aksesori

Item dikirim	Klem pemasangan: 1
--------------	--------------------

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Kabel: 2 m, PVC; 3 x 0.5 mm²

Koneksi



BN =	Warna core :
BU =	coklat
BK =	biru
	hitam