

IGKC012-ASKG/M/US-104-DRS/2LED



Jangkauan pendeteksian	[mm]	12
------------------------	------	----



Sensor induktif

IGKC012-ASKG/M/US-104-DRS/2LED

Jangkauan pendeteksian real Sr	[mm]	12 ± 10 %
Jarak pengoperasian	[mm]	0...9.7
Jangkauan pendeteksian yang lebih baik		ya
Akurasi/deviasi		
Faktor koreksi		baja: 1 / baja tahan karat: 0.7 / kuningan: 0.5 / aluminium: 0.4 / tembaga: 0.3
Histeresis	[X01]	3...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...70
Perlindungan		IP 68; ("Coolant")
Pengujian/persetujuan		
EME	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF dipancarkan	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF dihantarkan	10 V
	EN 55011	kelas B
MTTF	[ANN]	1056
Persetujuan UL	Ta	0...40 °C
	Tipe penutup	Type 1
	suplai tegangan	Hazardous voltage
	Nomor file UL	E174191
Data teknis		
Berat	[g]	50.5
Casing		tipe berulir
Pemasangan		non-flush mountable
Dimensi	[mm]	M18 x 1 / L = 70
Penamaan ulir		M18 x 1
Material		kuningan dilapisi perunggu putih; permukaan pendeteksian: PBT
Elemen display/pengoperasian		
Display	status peralihan	4 x 90° LED, kuning
	alat bantuan pengaturan	1 x LED, merah
Alat bantu pengaturan optik		ya
Aksesori		
Item dikirim		mur pengunci: 2
Keterangan		
Jumlah paket		1 buah

Sensor induktif

IGKC012-ASKG/M/US-104-DRS/2LED

Koneksi listrik - colokan

Konektor: 1 x M12; pengkodean: A; Kontak: dilapisi emas

