


Sensor induktif

IDC2050BARKA/LS-100AK



Karakteristik produk

Fungsi output		biasanya terbuka
Jangkauan pendeteksian [mm]		50
Casing		persegi panjang
Dimensi [mm]		92 x 80 x 40

Data kelistrikan

Frekuensi AC [Hz]		47...63
Tegangan pengoperasian [V]		20...140 AC / 10...140 DC
Kelas perlindungan		I
Pelindung polaritas terbalik		ya

Output

Fungsi output		biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]		6
Penurunan tegangan maks. pada output peralihan AC [V]		6
Arus beban minimal [mA]		5.5
Kebocoran arus maks. [mA]		1.7 (140 V AC/DC)
Peringkat arus permanen dari output peralihan AC [mA]		450
Peringkat arus permanen dari output peralihan DC [mA]		450
Peringkat arus jangka pendek dari output peralihan [mA]		2200; (20 ms / 0,5 Hz)
Frekuensi peralihan AC [Hz]		25
Frekuensi peralihan DC [Hz]		25



Sensor induktif

IDC2050BARKA/LS-100AK

Pelindung hubung singkat		ya	
Tipe pelindung hubung singkat		berpulsa	
Pelindung beban berlebih		ya	
Zona pendeteksian			
Jangkauan pendeteksian	[mm]	50	
Jarak pengoperasian	[mm]	0...40.5; (flush mountable dengan baja ringan (ST37))	
Akurasi/deviasi			
Faktor koreksi		baja: 1 / baja tahan karat: 0.85 / kuningan: 0.48 / aluminium: 0.46 / tembaga: 0.38	
Histeresis	[X01]	3...20	
Deviasi titik peralihan	[X01]	-15...15	
Kondisi pengoperasian			
Suhu sekitar	[°C]	-25...70	
Perlindungan		IP 67	
Pengujian/persetujuan			
EME		EN 60947-5-2	
MTTF	[ANN]	352	
Persetujuan UL		Ta	0...40 °C
		Tipe penutup	Type 1
		suplai tegangan	Hazardous voltage
		Nomor file UL	E174191
Data teknis			
Berat	[g]	427	
Casing		persegi panjang	
Pemasangan		flush mountable	
Dimensi	[mm]	92 x 80 x 40	
Material		PPE; seng tuang; kuningan berlapis nikel	
Elemen display/pengoperasian			
Display		status peralihan	1 x LED, merah
		operasi	1 x LED, hijau
		hubung singkat	1 x LED, hijau/merah berkedip secara bergantian
Aksesori			
Item dikirim		colokan penyegel: 1	
Keterangan			
Jumlah paket		1 buah	

Sensor induktif

IDC2050BARKA/LS-100AK

Koneksi listrik - colokan

Konektor: 1 x 1/2"; pengkodean: C

