

Sensor induktif

ID-2050-ARKG/6M/PVC

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	50
Casing	persegi panjang
Dimensi [mm]	120 x 80 x 30

Data kelistrikan

Tegangan pengoperasian [V]	10...55 DC
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	4.5
Arus beban minimal [mA]	5
Kebocoran arus maks. [mA]	0.6
Peringkat arus permanen dari output peralihan DC [mA]	100
Frekuensi peralihan DC [Hz]	8
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya



Sensor induktif

ID-2050-ARKG/6M/PVC

Zona pendeteksian		
Jangkauan pendeteksian	[mm]	50
Jangkauan pendeteksian dapat disesuaikan		ya
Jangkauan pendeteksian pengaturan pabrik	[mm]	50
Jangkauan pendeteksian real Sr	[mm]	50 ± 10 %
Jarak pengoperasian	[mm]	0...40.5
Akurasi/deviasi		
Faktor koreksi		baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 65
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing		persegi panjang
Pemasangan		non-flush mountable
Dimensi	[mm]	120 x 80 x 30
Material		PPE dimodifikasi
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		obeng: 1
Keterangan		
Jumlah paket		1 buah

ID9213



Sensor induktif

ID-2050-ARKG/6M/PVC

Koneksi listrik

Kabel: 6 m, PVC; 2 x 0.34 mm²

Koneksi



BK =

Warna core :
hitam