


Sensor induktif

IDC2050BARKG/UP/US-100 RT



Karakteristik produk

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	50
Casing	persegi panjang
Dimensi [mm]	92 x 80 x 40

Data kelistrikan

Tegangan pengoperasian [V]	10...55 DC
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	4.6
Arus beban minimal [mA]	4
Kebocoran arus maks. [mA]	0.6
Peringkat arus permanen dari output peralihan DC [mA]	400
Frekuensi peralihan DC [Hz]	90
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya



Sensor induktif

IDC2050BARKG/UP/US-100 RT

Zona pendeteksian		
Jangkauan pendeteksian	[mm]	50
Jarak pengoperasian	[mm]	0...40.5; (flush mountable dengan baja ringan (ST37))
Akurasi/deviasi		
Faktor koreksi		baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2
Histeresis	[X01]	3...20
Deviasi titik peralihan	[X01]	-15...15
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...70
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
MTTF	[ANN]	1631
Data teknis		
Berat	[g]	399
Casing		persegi panjang
Pemasangan		flush mountable
Tipe pemasangan		rel; (TH35 (EN 60715))
Dimensi	[mm]	92 x 80 x 40
Material		PPE; kuningan berlapis nikel
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, merah
Aksesori		
Item dikirim		colokan penyegel: 1
Keterangan		
Jumlah paket		1 buah
Koneksi listrik - colokan		

Konektor: 1 x M12; pengkodean: A





Sensor induktif

IDC2050BARKG/UP/US-100 RT

Koneksi

