

Sensor induktif

IEB3003-BPKG/V4A/2,5M/US RT



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	3
Casing	tipe berulir
Dimensi [mm]	M8 x 1 / L = 35

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	< 15
Kelas perlindungan	III
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	200
Frekuensi peralihan DC [Hz]	300
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian

Jangkauan pendeteksian [mm]	3
Jangkauan pendeteksian real Sr [mm]	$3 \pm 10\%$
Jarak pengoperasian [mm]	0...2.4

Akurasi/deviasi

Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.5 / aluminium: 0.4 / tembaga: 0.3
Histeresis [X01]	1...15
Deviasi titik peralihan [X01]	-10...10

Kondisi pengoperasian

Suhu sekitar [°C]	0...70
-------------------	--------



Sensor induktif

IEB3003-BPKG/V4A/2,5M/US RT

Perlindungan	IP 67
--------------	-------

Pengujian/persetujuan

EME	EN 60947-5-2	
	EN 55011	kelas B
MTTF	[ANN]	2819

Data teknis

Berat	[g]	90.5
Casing		tipe berulir
Pemasangan		non-flush mountable
Dimensi	[mm]	M8 x 1 / L = 35
Penamaan ulir		M8 x 1
Material		baja tahan karat; permukaan pendeteksian: PBT

Elemen display/pengoperasian

Display	status peralihan	1 x LED, merah
---------	------------------	----------------

Aksesori

Item dikirim		mur pengunci: 2
--------------	--	-----------------

Keterangan

Jumlah paket		1 buah
--------------	--	--------

Koneksi listrik - colokan

Kabel: 2.5 m, PVC; 3 x 0.14 mm²

Konektor: 1 x M12; pengkodean: A



Koneksi

