


Sensor induktif

IFC2004-ARKG/US

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	4
Casing	tipe berulir
Dimensi [mm]	M12 x 1

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	4.6
Arus beban minimal [mA]	4
Kebocoran arus maks. [mA]	0.6
Peringkat arus permanen dari output peralihan DC [mA]	150
Frekuensi peralihan DC [Hz]	1500
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa



Sensor induktif

IFC2004-ARKG/US

Pelindung beban berlebih	ya
--------------------------	----

Zona pendeteksian

Jangkauan pendeteksian [mm]	4
Jangkauan pendeteksian real Sr [mm]	$4 \pm 10 \%$
Jarak pengoperasian [mm]	0...3.25

Akurasi/deviasi

Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2	
Histeresis [X01]	1...15	
Deviasi titik peralihan [X01]	-10...10	

Kondisi pengoperasian

Suhu sekitar [°C]	-25...80
Perlindungan	IP 65

Pengujian/persetujuan

EME	EN 60947-5-2	
	EN 55011	kelas B

Data teknis

Casing	tipe berulir
Pemasangan	non-flush mountable
Dimensi [mm]	M12 x 1
Penamaan ulir	M12 x 1
Material	PBT

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
---------	------------------	-----------------

Aksesori


Item dikirim	mur pengunci: 2
--------------	-----------------

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik - soket

Konektor: 1 x M12; pengkodean: A





Sensor induktif

IFC2004-ARKG/US

Koneksi

