



Fungsi output		biasanya tertutup
Jangkauan pendeteksian	[mm]	8
Casing		tipe berulir
Dimensi	[mm]	M18 x 1 / L = 80

Tegangan pengoperasian	[V]	20...250 AC/DC
Kelas perlindungan		II
Pelindung polaritas terbalik		tidak

Fungsi output		biasanya tertutup
Penurunan tegangan maks. pada output peralihan DC	[V]	6
Penurunan tegangan maks. pada output peralihan AC	[V]	6.5
Arus beban minimal	[mA]	5
Kebocoran arus maks.	[mA]	2.5 (250 V AC) / 1.3 (110 V AC) / 0.8 (24 V DC)
Peringkat arus permanen dari output peralihan AC	[mA]	250; (350 (...50 °C))
Peringkat arus permanen dari output peralihan DC	[mA]	100
Peringkat arus jangka pendek dari output peralihan	[mA]	2200; (20 ms / 0,5 Hz)
Frekuensi peralihan AC	[Hz]	25
Frekuensi peralihan DC	[Hz]	50
Pelindung hubung singkat		tidak
Pelindung beban berlebih		tidak


Jangkauan pendeteksian	[mm]	8
Jangkauan pendeteksian real Sr	[mm]	$8 \pm 10 \%$
Jarak pengoperasian	[mm]	0...6.5



Sensor induktif

IGA2008-ABOA/SL

Akurasi/deviasi		
Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.5 / aluminium: 0.5 / tembaga: 0.4	
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan	IP 67	
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing	tipe berulir	
Pemasangan	non-flush mountable	
Dimensi	[mm]	M18 x 1 / L = 80
Penamaan ulir	M18 x 1	
Material	kuningan berlapis nikel; ULTRASON	
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim	mur pengunci: 2	
Keterangan		
Jumlah paket	1 buah	
Koneksi listrik		
Kabel: 2 m, PVC; 2 x 0.5 mm²		
Koneksi		



BN = Warna core :
 BU = coklat
 GN = biru
 hijau