

IGK3005UBPKG/SC/US-104-DPS



Jangkauan pendeteksian [mm]	5
Jangkauan pendeteksian real [mm] Sr	$5 \pm 10 \%$



Sensor induktif

IGK3005UBPKG/SC/US-104-DPS

Jarak pengoperasian	[mm]	0...4.05
---------------------	------	----------

Akurasi/deviasi

Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2	
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-10...10

Kondisi pengoperasian

Suhu sekitar	[°C]	-25...70
Perlindungan		IP 67

Pengujian/persetujuan

EME	EN 60947-5-2	
	EN 55011	kelas B
MTTF	[ANN]	1434
Persetujuan UL	Ta	0...40 °C
	Tipe penutup	Type 1
	suplai tegangan	Hazardous voltage
	Nomor file UL	E174191

Data teknis

Berat	[g]	65.5
Casing		tipe berulir
Pemasangan		flush mountable
Dimensi	[mm]	M18 x 1 / L = 60
Penamaan ulir		M18 x 1
Material		kuningan dilapisi PTFE; permukaan pendeteksian: PTFE

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
---------	------------------	-----------------

Aksesori

Item dikirim	mur pengunci: 2	
--------------	-----------------	--

Keterangan

Jumlah paket	1 buah	
--------------	--------	--

Koneksi listrik - colokan

Konektor: 1 x M12; pengkodean: A



Sensor induktif

IGK3005UBPKG/SC/US-104-DPS

Koneksi

