


Sensor induktif

IGK3008-BPKG/US-104



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	8
Casing	tipe berulir
Dimensi [mm]	M18 x 1 / L = 70

Aplikasi

Fitur khusus	Kontak berlapis emas
--------------	----------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	< 10
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	200
Frekuensi peralihan DC [Hz]	300
Pelindung hubung singkat	ya
Pelindung beban berlebih	ya

Zona pendeteksian

Jangkauan pendeteksian [mm]	8
Jangkauan pendeteksian real Sr	8 ± 10 %
Jarak pengoperasian [mm]	0...6.48

Akurasi/deviasi

Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.5 / aluminium: 0.4 / tembaga: 0.3
Histeresis [X01]	3...15
Deviasi titik peralihan [X01]	-10...10




Sensor induktif

IGK3008-BPKG/US-104

Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
MTTF	[ANN]	1083
Termasuk software yang disematkan		tidak
Data teknis		
Berat	[g]	54
Casing		tipe berulir
Pemasangan		non-flush mountable
Dimensi	[mm]	M18 x 1 / L = 70
Penamaan ulir		M18 x 1
Material		casing: kuningan dilapisi perunggu putih; permukaan pendeteksi: PBT oranye; Jendela LED: PEI; mur pengunci: kuningan dilapisi perunggu putih
Elemen display/pengoperasian		
Display	status peralihan	4 x LED, kuning
Aksesori		
Item dikirim		mur pengunci: 2
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		



Koneksi



IG5938



Sensor induktif

IGK3008-BPKG/US-104

Koneksi listrik - colokan

Konektor: 1 x M12; Kontak: dilapisi emas