

Sensor induktif

IGB3005-BNOG/ 6m

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	NPN
Fungsi output	biasanya tertutup
Jangkauan pendeteksian [mm]	5
Casing	tipe berulir
Dimensi [mm]	M18 x 1 / L = 38

Data kelistrikan

Tegangan pengoperasian [V]	18...36 DC
Konsumsi arus [mA]	15; (24 V)
Kelas perlindungan	II
Pelindung polaritas terbalik	tidak

Output

Desain kelistrikan	NPN
Fungsi output	biasanya tertutup
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	125; (150 (...50 °C))
Frekuensi peralihan DC [Hz]	500
Pelindung hubung singkat	tidak
Pelindung beban berlebih	tidak

Zona pendeteksian

Jangkauan pendeteksian [mm]	5
Jangkauan pendeteksian real Sr [mm]	5 ± 10 %
Jarak pengoperasian [mm]	0...4.05

Akurasi/deviasi

Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2
Histeresis [X01]	1...15
Deviasi titik peralihan [X01]	-10...10

Kondisi pengoperasian


Suhu sekitar [°C]	-25...80
Perlindungan	IP 67



Sensor induktif

IGB3005-BNOG/ 6m

Data teknis		
Casing	tipe berulir	
Pemasangan	flush mountable	
Dimensi	[mm]	M18 x 1 / L = 38
Penamaan ulir	M18 x 1	
Material	kuningan berlapis nikel; PBT	
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim	mur pengunci: 2	
Keterangan		
Jumlah paket	1 buah	
Koneksi listrik		
Kabel: 6 m, PVC; 3 x 0.5 mm ²		
Koneksi		



BN = Warna core :
 BK = coklat
 BU = biru
 hitam