


Sensor induktif

IGB3008-BPKG/10M/PVC/TOUT/INOX

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	8
Casing	tipe berulir
Dimensi [mm]	M18 x 1

Data kelistrikan

Tegangan pengoperasian [V]	18...36 DC
Konsumsi arus [mA]	15; (24 V)
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	125; (150 (...50 °C))
Frekuensi peralihan DC [Hz]	200
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya



Sensor induktif

IGB3008-BPKG/10M/PVC/TOUT/INOX

Zona pendeteksian		
Jangkauan pendeteksian	[mm]	8
Jangkauan pendeteksian real Sr	[mm]	8 ± 10 %
Jarak pengoperasian	[mm]	0...6.5
Akurasi/deviasi		
Faktor koreksi		baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing		tipe berulir
Pemasangan		non-flush mountable
Dimensi	[mm]	M18 x 1
Penamaan ulir		M18 x 1
Material		PBT; baja tahan karat (1.4404 / 316L)
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		mur pengunci: 2
Keterangan		
Jumlah paket		1 buah

IG9516




Sensor induktif

IGB3008-BPKG/10M/PVC/TOUT/INOX

Koneksi listrik

Kabel: 10 m, PVC; 3 x 0.34 mm²

Koneksi



BK = Warna core :
BN = hitam
BU = coklat
 biru