


Sensor induktif

IIA2010LBBOA/V4A/BS-301-A

Produk tidak tersedia - entri arsip



Karakteristik produk

Fungsi output		biasanya tertutup
Jangkauan pendeteksian [mm]		10
Casing		tipe berulir
Dimensi [mm]		M30 x 1.5

Data kelistrikan

Frekuensi AC [Hz]		47...63
Tegangan pengoperasian [V]		20...250 AC / 15...250 DC
Kelas perlindungan		II
Pelindung polaritas terbalik		tidak

Output

Fungsi output		biasanya tertutup
Penurunan tegangan maks. pada output peralihan DC [V]		6
Penurunan tegangan maks. pada output peralihan AC [V]		6.5
Arus beban minimal [mA]		5
Kebocoran arus maks. [mA]		2.5 (250 V AC) / 1.3 (110 V AC) / 0.8 (24 V DC)
Peringkat arus permanen dari output peralihan AC [mA]		250; (350 (...50 °C))
Peringkat arus permanen dari output peralihan DC [mA]		100
Frekuensi peralihan AC [Hz]		25
Frekuensi peralihan DC [Hz]		30
Pelindung hubung singkat		tidak
Pelindung beban berlebih		tidak



Sensor induktif

IIA2010LBBOA/V4A/BS-301-A

Zona pendeteksian		
Jangkauan pendeteksian	[mm]	10
Jangkauan pendeteksian real Sr	[mm]	10 ± 10 %
Jarak pengoperasian	[mm]	0...8.1
Akurasi/deviasi		
Faktor koreksi		baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.4 / tembaga: 0.3
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 67
Data teknis		
Casing		tipe berulir
Pemasangan		flush mountable
Dimensi	[mm]	M30 x 1.5
Penamaan ulir		M30 x 1.5
Material		baja tahan karat (1.4571 / 316Ti); PBT
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		mur pengunci: 2
Keterangan		
Jumlah paket		1 buah

Sensor induktif

IIA2010LBBOA/V4A/BS-301-A

Koneksi listrik - colokan

Konektor: 1 x M18; pengkodean: A

