


Sensor induktif

II-2010-ABOW/20m

Produk tidak tersedia - entri arsip



Karakteristik produk

Fungsi output		biasanya terbuka
Jangkauan pendeteksian	[mm]	10
Casing		tipe berulir
Dimensi	[mm]	M30 x 1.5

Data kelistrikan

Frekuensi AC	[Hz]	47...63
Tegangan pengoperasian	[V]	20...250 AC
Kelas perlindungan		II
Pelindung polaritas terbalik		tidak

Output


Fungsi output		biasanya terbuka
Penurunan tegangan maks. pada output peralihan AC	[V]	5.5
Arus beban minimal	[mA]	5
Kebocoran arus maks.	[mA]	2.5
Peringkat arus permanen dari output peralihan AC	[mA]	300; (500 (...50 °C))
Peringkat arus jangka pendek dari output peralihan	[mA]	2200; (20 ms / 0,5 Hz)
Frekuensi peralihan AC	[Hz]	20
Pelindung hubung singkat		tidak
Pelindung beban berlebih		tidak



Sensor induktif

II-2010-ABOW/20m

Zona pendeteksian		
Jangkauan pendeteksian	[mm]	10
Jangkauan pendeteksian real Sr	[mm]	10 ± 10 %
Jarak pengoperasian	[mm]	0...8.1
Akurasi/deviasi		
Faktor koreksi		baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.4 / tembaga: 0.3
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 67
Data teknis		
Casing		tipe berulir
Pemasangan		flush mountable
Dimensi	[mm]	M30 x 1.5
Penamaan ulir		M30 x 1.5
Material		PBT
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		mur pengunci: 2
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 20 m, PVC; 2 x 0.5 mm ²		
Koneksi		



BN = Warna core :
 BU = coklat
 biru