


Sensor induktif

IIK3010-BPOG/ 3mPPU

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	10
Casing	tipe berulir
Dimensi [mm]	M30 x 1.5

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	< 15
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	200
Frekuensi peralihan DC [Hz]	200
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya




Sensor induktif

IIK3010-BPOG/ 3mPPU

Zona pendeteksian		
Jangkauan pendeteksian	[mm]	10
Jangkauan pendeteksian real Sr	[mm]	10 ± 10 %
Jarak pengoperasian	[mm]	0...8.1
Akurasi/deviasi		
Faktor koreksi		baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing		tipe berulir
Pemasangan		flush mountable
Dimensi	[mm]	M30 x 1.5
Penamaan ulir		M30 x 1.5
Material		casing: kuningan dilapisi perunggu putih; permukaan pendeteksian: PBT
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		mur pengunci: 2
Keterangan		
Jumlah paket		1 buah

**Sensor induktif**

IIK3010-BPOG/ 3mPPU

Koneksi listrikKabel: 3 m, PUR / PVC; 3 x 0.5 mm²**Koneksi**

BK = Warna core :
BN = hitam
BU = coklat
 biru