


IIA3015-BPKG/V4A/US-104





## Sensor induktif

IIA3015-BPKG/V4A/US-104

| Akurasi/deviasi                                         |                                                                                 |                                                                                                                                               |
|---------------------------------------------------------|---------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Faktor koreksi                                          | baja: 1 / baja tahan karat: 0.7 / kuningan: 0.5 / aluminium: 0.4 / tembaga: 0.3 |                                                                                                                                               |
| Histeresis                                              | [X01]                                                                           | 1...20                                                                                                                                        |
| Deviasi titik peralihan                                 | [X01]                                                                           | -10...10                                                                                                                                      |
| Kondisi pengoperasian                                   |                                                                                 |                                                                                                                                               |
| Suhu sekitar                                            | [°C]                                                                            | -25...80                                                                                                                                      |
| Perlindungan                                            |                                                                                 | IP 67                                                                                                                                         |
| Pengujian/persetujuan                                   |                                                                                 |                                                                                                                                               |
| EME                                                     | EN 61000-4-2 ESD                                                                | 4 kV CD / 8 kV AD                                                                                                                             |
|                                                         | EN 61000-4-3 HF dipancarkan                                                     | 10 V/m                                                                                                                                        |
|                                                         | EN 61000-4-4 Burst                                                              | 2 kV                                                                                                                                          |
|                                                         | EN 61000-4-6 HF dihantarkan                                                     | 10 V                                                                                                                                          |
|                                                         | EN 55011                                                                        | kelas B                                                                                                                                       |
| MTTF                                                    | [ANN]                                                                           | 1083                                                                                                                                          |
| Data teknis                                             |                                                                                 |                                                                                                                                               |
| Berat                                                   | [g]                                                                             | 149.5                                                                                                                                         |
| Casing                                                  |                                                                                 | tipe berulir                                                                                                                                  |
| Pemasangan                                              |                                                                                 | non-flush mountable                                                                                                                           |
| Dimensi                                                 | [mm]                                                                            | M30 x 1.5 / L = 75                                                                                                                            |
| Penamaan ulir                                           |                                                                                 | M30 x 1.5                                                                                                                                     |
| Material                                                |                                                                                 | casing: baja tahan karat (1.4404 / 316L); permukaan pendeteksian: PBT putih; Jendela LED: PEI; mur pengunci: baja tahan karat (1.4404 / 316L) |
| Torsi pengencangan                                      | [Nm]                                                                            | 80                                                                                                                                            |
| Elemen display/pengoperasian                            |                                                                                 |                                                                                                                                               |
| Display                                                 | status peralihan                                                                | 4 x LED, kuning                                                                                                                               |
| Aksesori                                                |                                                                                 |                                                                                                                                               |
| Item dikirim                                            |                                                                                 | mur pengunci: 2                                                                                                                               |
| Keterangan                                              |                                                                                 |                                                                                                                                               |
| Jumlah paket                                            |                                                                                 | 1 buah                                                                                                                                        |
| Koneksi listrik - colokan                               |                                                                                 |                                                                                                                                               |
| Konektor: 1 x M12; pengkodean: A; Kontak: dilapisi emas |                                                                                 |                                                                                                                                               |



# II5776



## Sensor induktif

IIA3015-BPKG/V4A/US-104

### Koneksi

