


Sensor induktif

IIB2010-BBOW/SL/LS-100AK

Produk tidak tersedia - entri arsip



Karakteristik produk

Fungsi output		biasanya tertutup
Jangkauan pendeteksian	[mm]	10
Casing		tipe berulir
Dimensi	[mm]	M30 x 1.5

Data kelistrikan

Frekuensi AC	[Hz]	47...63
Tegangan pengoperasian	[V]	80...140 AC
Pelindung polaritas terbalik		tidak

Output

Fungsi output		biasanya tertutup
Penurunan tegangan maks. pada output peralihan AC	[V]	8.5
Arus beban minimal	[mA]	5
Kebocoran arus maks.	[mA]	1.7
Peringkat arus permanen dari output peralihan AC	[mA]	200
Peringkat arus jangka pendek dari output peralihan	[mA]	900; (20 ms / 0,5 Hz)
Frekuensi peralihan AC	[Hz]	20
Pelindung hubung singkat		tidak
Pelindung beban berlebih		tidak

Zona pendeteksian

Jangkauan pendeteksian	[mm]	10
------------------------	------	----



Sensor induktif

IIB2010-BBOW/SL/LS-100AK

Jangkauan pendeteksian real [mm] Sr	10 ± 10 %
Jarak pengoperasian [mm]	0...8.1

Akurasi/deviasi

Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.5 / aluminium: 0.4 / tembaga: 0.3	
Histeresis [X01]	3...15	
Deviasi titik peralihan [X01]	-10...10	

Kondisi pengoperasian

Suhu sekitar [°C]	-25...80
Perlindungan	IP 65

Pengujian/persetujuan

EME	EN 60947-5-2	
	EN 55011	kelas B

Data teknis

Casing	tipe berulir
Pemasangan	flush mountable
Dimensi [mm]	M30 x 1.5
Penamaan ulir	M30 x 1.5
Material	kuningan berlapis nikel; PBT

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
---------	------------------	-----------------

Aksesori

Item dikirim	mur pengunci: 2
--------------	-----------------

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik - colokan

Konektor: 1 x 1/2"; pengkodean: C





Sensor induktif

IIB2010-BBOW/SL/LS-100AK

Koneksi

