


Sensor induktif

IIC4015-CPKG/30M

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	komplementer
Jangkauan pendeteksian [mm]	15
Casing	tipe berulir
Dimensi [mm]	M30 x 1.5

Aplikasi

Fitur khusus	Bebas halogen
--------------	---------------

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	15; (24 V)
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	komplementer
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	250
Pelindung hubung singkat	ya




Sensor induktif

IIC4015-CPKG/30M

Tipe pelindung hubung singkat	berpulsa	
Pelindung beban berlebih	ya	
Zona pendeteksian		
Jangkauan pendeteksian [mm]	15	
Jangkauan pendeteksian real Sr [mm]	15 ± 10 %	
Jarak pengoperasian [mm]	0...12.1	
Akurasi/deviasi		
Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.5 / aluminium: 0.4 / tembaga: 0.3	
Histeresis [X01]	3...15	
Deviasi titik peralihan [X01]	-10...10	
Kondisi pengoperasian		
Suhu sekitar [°C]	-25...80	
Perlindungan	IP 68	
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing	tipe berulir	
Pemasangan	non-flush mountable	
Dimensi [mm]	M30 x 1.5	
Penamaan ulir	M30 x 1.5	
Material	PBT; TPE-E	
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim	mur pengunci: 2	
Keterangan		
Jumlah paket	1 buah	

**Sensor induktif**

IIC4015-CPKG/30M

Koneksi listrikKabel: 30 m, PUR, Bebas halogen; 4 x 0.34 mm²**Koneksi**

BK =	Warna core :
BN =	hitam
BU =	coklat
WH =	biru
	putih