


Sensor induktif

II-3010-BNKG/10m

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	NPN
Fungsi output	biasanya tertutup
Jangkauan pendeteksian [mm]	10
Casing	tipe berulir
Dimensi [mm]	M30 x 1.5 / L = 81

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	15; (24 V)
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	NPN
Fungsi output	biasanya tertutup
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	250
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian


Jangkauan pendeteksian [mm]	10
Jangkauan pendeteksian real Sr	10 ± 10 %
Jarak pengoperasian [mm]	0...8.1



Sensor induktif

II-3010-BNKG/10m

Akurasi/deviasi		
Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2	
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan	IP 67	
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing	tipe berulir	
Pemasangan	flush mountable	
Dimensi	[mm]	M30 x 1.5 / L = 81
Penamaan ulir	M30 x 1.5	
Material	PBT	
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim	mur pengunci: 2	
Keterangan		
Jumlah paket	1 buah	
Koneksi listrik		
Kabel: 10 m, PVC; 3 x 0.5 mm²		
Koneksi		



BN = Warna core :
 BU = coklat
 BK = biru
 hitam