


Sensor induktif

II-2015-ARKG/UP/6M

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	15
Casing	tipe berulir
Dimensi [mm]	M30 x 1.5

Data kelistrikan

Tegangan pengoperasian [V]	10...55 DC
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	4.6
Arus beban minimal [mA]	4
Kebocoran arus maks. [mA]	0.5
Peringkat arus permanen dari output peralihan DC [mA]	400
Frekuensi peralihan DC [Hz]	200
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa



Sensor induktif

II-2015-ARKG/UP/6M

Pelindung beban berlebih	ya	
Zona pendeteksian		
Jangkauan pendeteksian	[mm]	15
Jangkauan pendeteksian real Sr	[mm]	15 ± 10 %
Jarak pengoperasian	[mm]	0...12.1
Akurasi/deviasi		
Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2	
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan	IP 67	
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing	tipe berulir	
Pemasangan	non-flush mountable	
Dimensi	[mm]	M30 x 1.5
Penamaan ulir	M30 x 1.5	
Material	PBT	
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim	mur pengunci: 2	
Keterangan		
Jumlah paket	1 buah	

II9213



Sensor induktif

II-2015-ARKG/UP/6M

Koneksi listrik

Kabel: 6 m, PVC; 2 x 0.34 mm²

Koneksi



BK =

Warna core :
hitam