


Sensor induktif

IIB3015-BPKG



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	15
Casing	tipe berulir
Dimensi [mm]	M30 x 1.5 / L = 45

Data kelistrikan

Tegangan pengoperasian [V]	18...36 DC
Konsumsi arus [mA]	15; (24 V)
Kelas perlindungan	III
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	125; (150 (...50 °C))
Frekuensi peralihan DC [Hz]	250
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian

Jangkauan pendeteksian [mm]	15
Jangkauan pendeteksian real Sr [mm]	15 ± 10 %
Jarak pengoperasian [mm]	0...12.15

Akurasi/deviasi


Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2
Histeresis [X01]	1...15



Sensor induktif

IIB3015-BPKG

Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 60947-5-2	
MTTF	[ANN]	901
Data teknis		
Berat	[g]	210.5
Casing		tipe berulir
Pemasangan		non-flush mountable
Dimensi	[mm]	M30 x 1.5 / L = 45
Penamaan ulir		M30 x 1.5
Material		kuningan berlapis nikel; permukaan pendeteksian: PBT
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim		mur pengunci: 2
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 2 m, PVC; 3 x 0.5 mm ²		
Koneksi		



BN = Warna core :
 BU = coklat
 BK = biru
 hitam