




Sensor induktif

ILB30,8-BPKG/2M PVC



1 permukaan pendeteksian



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	0.8
Casing	persegi panjang
Dimensi [mm]	25 x 5 x 5

Data kelistrikan

Tegangan pengoperasian [V]	10...30 DC
Konsumsi arus [mA]	10; (24 V)
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	1
Peringkat arus permanen dari output peralihan DC [mA]	100
Frekuensi peralihan DC [Hz]	1000
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	tidak

Zona pendeteksian

Jangkauan pendeteksian [mm]	0.8
-----------------------------	-----

**Sensor induktif**

ILB30,8-BPKG/2M PVC

Jangkauan pendeteksian real Sr	[mm]	0.8 ± 10 %	
Jarak pengoperasian	[mm]	0...0.65	
Akurasi/deviasi			
Faktor koreksi		baja: 1 / baja tahan karat: 0.7 / kuningan: 0.5 / aluminium: 0.4 / tembaga: 0.3	
Histeresis	[X01]	< 15	
Deviasi titik peralihan	[X01]	-10...10	
Kondisi pengoperasian			
Suhu sekitar	[°C]	-25...70	
Perlindungan		IP 67	
Pengujian/persetujuan			
EME		EN 60947-5-2	
		EN 55011	kelas B
MTTF	[ANN]	640	
Persetujuan UL		Ta	0...40 °C
		suplai tegangan	Class 2
		Nomor file UL	E174191
Data teknis			
Berat	[g]	54.5	
Casing		persegi panjang	
Pemasangan		flush mountable	
Dimensi	[mm]	25 x 5 x 5	
Material		casing: aluminium dianodisasi; permukaan pendeteksian: POM	
Elemen display/pengoperasian			
Display		status peralihan	1 x LED, merah
Aksesori			
Item dikirim		sekrup: 2	
Keterangan			
Jumlah paket		1 buah	

IL5022




Sensor induktif

ILB30,8-BPKG/2M PVC

Koneksi listrik

Kabel: 2 m, PVC; 3 x 0.14 mm²

Koneksi



	Warna core :
BK =	hitam
BN =	coklat
BU =	biru