


IN5411



Sensor induktif

INV2004DARKG/US

Produk tidak tersedia - entri arsip



- 1 sensor 1
- 2 sensor 2
- 3 LED OUT 1
- 4 LED OUT21



Karakteristik produk	
Desain kelistrikan	PNP/NPN
Fungsi output	2 x biasanya terbuka
Jangkauan pendeteksian [mm]	4
Casing	persegi panjang
Dimensi [mm]	33 x 60 x 64
Data kelistrikan	
Tegangan pengoperasian [V]	10...30 DC; (; sesuai PELV)
Kelas perlindungan	III
Pelindung polaritas terbalik	ya
Output	
Desain kelistrikan	PNP/NPN
Fungsi output	2 x biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	4.6



Sensor induktif

INV2004DARKG/US

Arus beban minimal	[mA]	4
Kebocoran arus maks.	[mA]	0.8
Peringkat arus permanen dari output peralihan DC	[mA]	100
Frekuensi peralihan DC	[Hz]	500
Pelindung hubung singkat		ya
Tipe pelindung hubung singkat		berpulsa
Pelindung beban berlebih		ya
Zona pendeteksian		
Jangkauan pendeteksian	[mm]	4
Jangkauan pendeteksian real Sr	[mm]	4 ± 10 %
Jarak pengoperasian	[mm]	0...3.25
Akurasi/deviasi		
Faktor koreksi		baja: 1 / baja tahan karat: 0.7 / kuningan: 0.5 / aluminium: 0.4 / tembaga: 0.3
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing		persegi panjang
Pemasangan		non-flush mountable
Dimensi	[mm]	33 x 60 x 64
Material		casing: PA; sekrup: baja tahan karat; washer: baja tahan karat
Elemen display/pengoperasian		
Display	status peralihan	2 x LED, kuning
Aksesori		
Item dikirim		washer: 2
		Sekrup silinder: 2 x M5 x 18
Keterangan		
Jumlah paket		1 buah

IN5411





Sensor induktif

INV2004DARKG/US

Koneksi listrik - colokan

Konektor: 1 x M12; pengkodean: A



BK =
BN =
BU =
WH =

Warna core :
hitam
coklat
biru
putih