




Sensor induktif

IMC2015-BRKG/UP/0.15M/PUR/US

Produk tidak tersedia - entri arsip



Karakteristik produk	
Desain kelistrikan	PNP/NPN
Fungsi output	biasanya tertutup
Jangkauan pendeteksian [mm]	15
Casing	persegi panjang
Dimensi [mm]	40 x 40 x 66
Aplikasi	
Fitur khusus	Kontak berlapis emas
Data kelistrikan	
Tegangan pengoperasian [V]	10...55 DC
Kelas perlindungan	II
Pelindung polaritas terbalik	ya
Output	
Desain kelistrikan	PNP/NPN



Sensor induktif

IMC2015-BRKG/UP/0.15M/PUR/US

Fungsi output	biasanya tertutup	
Penurunan tegangan maks. pada output peralihan DC [V]	4.6	
Arus beban minimal [mA]	2	
Kebocoran arus maks. [mA]	0.8	
Peringkat arus permanen dari output peralihan DC [mA]	100	
Frekuensi peralihan DC [Hz]	150	
Pelindung hubung singkat	ya	
Tipe pelindung hubung singkat	berpulsa	
Pelindung beban berlebih	ya	
Zona pendeteksian		
Jangkauan pendeteksian [mm]	15	
Jangkauan pendeteksian real Sr [mm]	15 ± 10 %	
Jarak pengoperasian [mm]	0...12.1	
Akurasi/deviasi		
Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2	
Histeresis [X01]	1...15	
Deviasi titik peralihan [X01]	-10...10	
Kondisi pengoperasian		
Suhu sekitar [°C]	-25...70	
Perlindungan	IP 67	
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing	persegi panjang	
Pemasangan	flush mountable	
Dimensi [mm]	40 x 40 x 66	
Material	casing: PBT; permukaan pendeteksian: PEI; klem: PPS	
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Aksesori		
Item dikirim	Braket pemasangan: 1	
	Kunci pas: 1	
Keterangan		
Jumlah paket	1 buah	

Sensor induktif

IMC2015-BRKG/UP/0.15M/PUR/US

Koneksi listrik - colokan

Kabel: 0.15 m, PUR

Konektor: 1 x M12; pengkodean: A; Kontak: dilapisi emas



Koneksi

