

IN5133



Sensor induktif

IN-3004-ANKG



- 1 lubang pemasangan
- 2 bushing berulir M3 kedalaman 5.8 mm
- 3 ilustrasi (contoh)




Karakteristik produk		
Desain kelistrikan		NPN
Fungsi output		biasanya terbuka
Jangkauan pendeteksian [mm]		4
Casing		persegi panjang
Dimensi [mm]		40 x 12 x 26
Data kelistrikan		
Tegangan pengoperasian [V]		10...36 DC
Konsumsi arus [mA]		15; (24 V)
Kelas perlindungan		II
Pelindung polaritas terbalik		ya
Output		
Desain kelistrikan		NPN
Fungsi output		biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]		2.5
Peringkat arus permanen dari output peralihan DC [mA]		250
Frekuensi peralihan DC [Hz]		1300
Pelindung hubung singkat		ya
Tipe pelindung hubung singkat		berpulsa
Pelindung beban berlebih		ya
Zona pendeteksian		
Jangkauan pendeteksian [mm]		4
Jangkauan pendeteksian real Sr		4 ± 10 %
Jarak pengoperasian [mm]		0...3.25



Sensor induktif

IN-3004-ANKG

Akurasi/deviasi		
Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2	
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan	IP 67	
Pengujian/persetujuan		
EME	EN 60947-5-2	kelas B
	EN 55011	
MTTF	[ANN]	1781
Data teknis		
Berat	[g]	112.9
Casing	persegi panjang	
Pemasangan	non-flush mountable	
Dimensi	[mm]	40 x 12 x 26
Material	PBT	
Lubang pemasangan		
Torsi pengencangan	[Nm]	< 0.5
Bushing berulir		
Torsi pengencangan	[Nm]	< 1.2; (ketika insert kuningan bersentuhan dengan pasangan komponen)
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Keterangan		
Jumlah paket	1 buah	
Koneksi listrik		
Kabel: 2 m, PVC; 3 x 0.5 mm²		
Koneksi		



BN = Warna core :
 BU = coklat
 BK = biru
 hitam