




Sensor induktif

IN-3002-APKG/15m

Produk tidak tersedia - entri arsip



- 1 lubang pemasangan
2 bushing berulir M3 kedalaman 5.8 mm
3 ilustrasi (contoh)



Karakteristik produk		
Desain kelistrikan		PNP
Fungsi output		biasanya tertutup
Jangkauan pendeteksian [mm]		2
Casing		persegi panjang
Dimensi [mm]		40 x 12 x 26
Data kelistrikan		
Tegangan pengoperasian [V]		10...36 DC
Konsumsi arus [mA]		15; (24 V)
Kelas perlindungan		II
Pelindung polaritas terbalik		ya
Output		
Desain kelistrikan		PNP
Fungsi output		biasanya tertutup
Penurunan tegangan maks. pada output peralihan DC [V]		2.5
Peringkat arus permanen dari output peralihan DC [mA]		250
Frekuensi peralihan DC [Hz]		1400
Pelindung hubung singkat		ya
Tipe pelindung hubung singkat		berpulsa
Pelindung beban berlebih		ya
Zona pendeteksian		
Jangkauan pendeteksian [mm]		2

IN5234



Sensor induktif

IN-3002-APKG/15m

Jangkauan pendeteksian real [mm] Sr	2 ± 10 %
Jarak pengoperasian [mm]	0...1.6

Akurasi/deviasi

Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2	
Histeresis [X01]	1...15	
Deviasi titik peralihan [X01]	-10...10	

Kondisi pengoperasian

Suhu sekitar [°C]	-25...80
Perlindungan	IP 67

Pengujian/persetujuan

EME	EN 60947-5-2	
MTTF [ANN]	1925	

Data teknis

Casing	persegi panjang
Pemasangan	flush mountable
Dimensi [mm]	40 x 12 x 26
Material	PBT

Lubang pemasangan

Torsi pengencangan [Nm]	< 0.5
-------------------------	-------

Bushing berulir

Torsi pengencangan [Nm]	< 1.2; (ketika insert kuningan bersentuhan dengan pasangan komponen)
-------------------------	--

Elemen display/pengoperasian

Display	status peralihan	1 x LED, kuning
---------	------------------	-----------------


Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik

Kabel: 15 m, PVC; 3 x 0.5 mm²

Koneksi



	Warna core :
BN =	coklat
BU =	biru
BK =	hitam