


Sensor ganda induktif untuk aktuatur katup

IND3004DBPKG/US-100-DPV



Karakteristik produk

Desain kelistrikan	PNP
Fungsi output	2 x biasanya terbuka
Jangkauan pendeteksian [mm]	4
Casing	persegi panjang
Dimensi [mm]	40 x 26 x 47

Aplikasi

Fitur khusus	Kontak berlapis emas
--------------	----------------------

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	15; (24 V)
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP
Fungsi output	2 x biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	250
Frekuensi peralihan DC [Hz]	1300
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya

Zona pendeteksian

Jangkauan pendeteksian [mm]	4
Jangkauan pendeteksian real Sr [mm]	4 ± 10 %
Jarak pengoperasian [mm]	0...3.25



Sensor ganda induktif untuk aktuatur katup

IND3004DBPKG/US-100-DPV

Akurasi/deviasi		
Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2	
Histeresis [X01]		1...15
Deviasi titik peralihan [X01]		-10...10
Kondisi pengoperasian		
Suhu sekitar [°C]		-25...80
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
MTTF [ANN]		1064
Persetujuan UL	Ta	0...40 °C
	Tipe penutup	Type 1
	suplai tegangan	Hazardous voltage
	Nomor file UL	E174191
Data teknis		
Berat [g]		57
Casing		persegi panjang
Pemasangan		non-flush mountable
Dimensi [mm]		40 x 26 x 47
Material		casing: PBT
Elemen display/pengoperasian		
Display	status peralihan	2 x LED, kuning
Keterangan		
Jumlah paket		1 buah
Koneksi listrik - colokan		
Konektor: 1 x M12; pengkodean: A; Bodi cetakan: baja tahan karat; Kontak: dilapisi emas		
		

IN5327



Sensor ganda induktif untuk aktuatur katup

IND3004DBPKG/US-100-DPV

Koneksi

