


Sensor induktif

IOC2010-ARKG/6M/PUR/ FRONT

Produk tidak tersedia - entri arsip



- 1 lubang pemasangan M4 diperkuat
2 Permukaan pendeteksian



Karakteristik produk

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	10
Casing	persegi panjang
Dimensi [mm]	26 x 26 x 42

Data kelistrikan

Tegangan pengoperasian [V]	10...55 DC
Kelas perlindungan	II
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	4.5
Arus beban minimal [mA]	2
Kebocoran arus maks. [mA]	0.6
Peringkat arus permanen dari output peralihan DC [mA]	100
Frekuensi peralihan DC [Hz]	250
Pelindung hubung singkat	ya



Sensor induktif

IOC2010-ARKG/6M/PUR/ FRONT

Tipe pelindung hubung singkat	berpulsa	
Pelindung beban berlebih	ya	
Zona pendeteksian		
Jangkauan pendeteksian [mm]	10	
Jangkauan pendeteksian real Sr [mm]	10 ± 10 %	
Jarak pengoperasian [mm]	0...8.1	
Akurasi/deviasi		
Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2	
Histeresis [X01]	1...15	
Deviasi titik peralihan [X01]	-10...10	
Kondisi pengoperasian		
Suhu sekitar [°C]	-25...80	
Perlindungan	IP 67	
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing	persegi panjang	
Permukaan pendeteksian	depan	
Pemasangan	flush mountable	
Dimensi [mm]	26 x 26 x 42	
Material	PBT	
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, merah
Keterangan		
Jumlah paket	1 buah	

IO5010





Sensor induktif

IOC2010-ARKG/6M/PUR/ FRONT

Koneksi listrik

Kabel: 6 m, PUR; 2 x 0.5 mm²

Koneksi



BN =
BU =

Warna core :
coklat
biru