




Sensor induktif

IOW2010-ARKG/UP/T/40CM PVC US

Produk tidak tersedia - entri arsip



1 lubang pemasangan M4 diperkuat



Karakteristik produk

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	10
Casing	persegi panjang
Dimensi [mm]	26 x 26 x 26

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	4.5
Arus beban minimal [mA]	2
Kebocoran arus maks. [mA]	0.6
Peringkat arus permanen dari output peralihan DC [mA]	100
Frekuensi peralihan DC [Hz]	50
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa



Sensor induktif

IOW2010-ARKG/UP/T/40CM PVC US

Pelindung beban berlebih	ya
--------------------------	----

Zona pendeteksian

Jangkauan pendeteksian [mm]	10
Jangkauan pendeteksian real Sr	$10 \pm 10 \%$
Jarak pengoperasian [mm]	0...8.1

Akurasi/deviasi

Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2	
Histeresis [X01]	1...15	
Deviasi titik peralihan [X01]	-10...10	

Kondisi pengoperasian

Suhu sekitar [°C]	0...70
Perlindungan	IP 65

Pengujian/persetujuan

EME	EN 60947-5-2	
	EN 55011	kelas B

Data teknis

Casing	persegi panjang
Pemasangan	flush mountable
Dimensi [mm]	26 x 26 x 26
Material	PTFE

Elemen display/pengoperasian

Display	status peralihan	1 x LED, merah
---------	------------------	----------------

Keterangan

Jumlah paket	1 buah
--------------	--------

Koneksi listrik - colokan

Kabel: 0.15 m, PVC

Konektor: 1 x M12; pengkodean: A





Sensor induktif

IOW2010-ARKG/UP/T/40CM PVC US

Koneksi

