




Sensor induktif

IO-2010-ARKG/12m PUR

Produk tidak tersedia - entri arsip



1 Permukaan pendeteksian



Karakteristik produk

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Jangkauan pendeteksian [mm]	10
Casing	persegi panjang
Dimensi [mm]	26 x 26 x 70

Data kelistrikan

Tegangan pengoperasian [V]	10...55 DC
Pelindung polaritas terbalik	ya

Output


Desain kelistrikan	PNP/NPN
Fungsi output	biasanya terbuka
Penurunan tegangan maks. pada output peralihan DC [V]	6.5
Arus beban minimal [mA]	5
Kebocoran arus maks. [mA]	0.6
Peringkat arus permanen dari output peralihan DC [mA]	100
Frekuensi peralihan DC [Hz]	100
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa



Sensor induktif

IO-2010-ARKG/12m PUR

Pelindung beban berlebih	ya	
Zona pendeteksian		
Jangkauan pendeteksian	[mm]	10
Jangkauan pendeteksian real Sr	[mm]	10 ± 10 %
Jarak pengoperasian	[mm]	0...8.1
Akurasi/deviasi		
Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.4 / tembaga: 0.3	
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan	IP 68	
Pengujian/persetujuan		
EME	EN 60947-5-2	
	EN 55011	kelas B
Data teknis		
Casing	persegi panjang	
Pemasangan	flush mountable	
Dimensi	[mm]	26 x 26 x 70
Material	PBT	
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Keterangan		
Jumlah paket	1 buah	
Koneksi listrik		
Kabel: 12 m, PUR; 2 x 0.5 mm²		
Koneksi		



BK = Warna core :
 hitam