


Sensor induktif

IS-3002-BNOG/10m

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	NPN
Fungsi output	biasanya tertutup
Jangkauan pendeteksian [mm]	2
Casing	persegi panjang
Dimensi [mm]	28 x 10 x 16

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	15; (24 V)
Kelas perlindungan	III
Pelindung polaritas terbalik	tidak

Output

Desain kelistrikan	NPN
Fungsi output	biasanya tertutup
Penurunan tegangan maks. pada output peralihan DC [V]	1
Peringkat arus permanen dari output peralihan DC [mA]	200
Frekuensi peralihan DC [Hz]	800
Pelindung hubung singkat	tidak
Pelindung beban berlebih	tidak

Zona pendeteksian


Jangkauan pendeteksian [mm]	2
Jangkauan pendeteksian real Sr	$2 \pm 10 \%$



Sensor induktif

IS-3002-BNOG/10m

Jarak pengoperasian	[mm]	0...1.6
Akurasi/deviasi		
Faktor koreksi		baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-20...80
Perlindungan		IP 67
Pengujian/persetujuan		
EME		EN 60947-5-2
MTTF	[ANN]	2791
Data teknis		
Casing		persegi panjang
Pemasangan		flush mountable
Dimensi	[mm]	28 x 10 x 16
Material		PBT
Torsi pengencangan	[Nm]	< 0.5; (dengan washer)
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 10 m, PVC; 3 x 0.14 mm ²		
Koneksi		



Warna core :

BN = coklat

BU = biru

BK = hitam