

Sensor induktif

IS-3002-BNKG/6M



Karakteristik produk

Desain kelistrikan	NPN
Fungsi output	biasanya tertutup
Jangkauan pendeteksian [mm]	2
Casing	persegi panjang
Dimensi [mm]	27.8 x 10.2 x 16

Data kelistrikan

Tegangan pengoperasian [V]	10...36 DC
Konsumsi arus [mA]	15; (24 V)
Kelas perlindungan	III
Pelindung polaritas terbalik	ya

Output

Desain kelistrikan	NPN
Fungsi output	biasanya tertutup
Penurunan tegangan maks. pada output peralihan DC [V]	2.5
Peringkat arus permanen dari output peralihan DC [mA]	200
Frekuensi peralihan DC [Hz]	800
Pelindung hubung singkat	ya
Pelindung beban berlebih	ya

Zona pendeteksian


Jangkauan pendeteksian [mm]	2
Jangkauan pendeteksian real Sr	$2 \pm 10 \%$
Jarak pengoperasian [mm]	0...1.6



Sensor induktif

IS-3002-BNKG/6M

Akurasi/deviasi		
Faktor koreksi	baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.3 / tembaga: 0.2	
Histeresis [X01]		1...15
Deviasi titik peralihan [X01]		-10...10
Kondisi pengoperasian		
Suhu sekitar [°C]		-20...80
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF dipancarkan	3 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF dihantarkan	3 V
	EN 55011	kelas B
MTTF [ANN]		2791
Data teknis		
Berat [g]		125
Casing		persegi panjang
Pemasangan		flush mountable
Dimensi [mm]		27.8 x 10.2 x 16
Material		PBT
Torsi pengencangan [Nm]		< 0.5; (dengan washer)
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 6 m, PVC; 3 x 0.14 mm ²		
Koneksi		



Warna core :

BN = coklat

BU = biru

BK = hitam