


Sensor induktif

IW-2008-BRKG/PPU

Produk tidak tersedia - entri arsip



Karakteristik produk

Desain kelistrikan	PNP/NPN
Fungsi output	biasanya tertutup
Jangkauan pendeteksian [mm]	8
Casing	persegi panjang
Dimensi [mm]	60 x 36 x 10

Data kelistrikan

Tegangan pengoperasian [V]	10...55 DC
Pelindung polaritas terbalik	ya

Output



Desain kelistrikan	PNP/NPN
Fungsi output	biasanya tertutup
Penurunan tegangan maks. pada output peralihan DC [V]	4.6
Arus beban minimal [mA]	4
Kebocoran arus maks. [mA]	0.6
Peringkat arus permanen dari output peralihan DC [mA]	100
Frekuensi peralihan DC [Hz]	300
Pelindung hubung singkat	ya
Tipe pelindung hubung singkat	berpulsa
Pelindung beban berlebih	ya



Sensor induktif

IW-2008-BRKG/PPU

Zona pendeteksian		
Jangkauan pendeteksian	[mm]	8
Jangkauan pendeteksian real Sr	[mm]	8 ± 10 %
Jarak pengoperasian	[mm]	0...6.5
Akurasi/deviasi		
Faktor koreksi		baja: 1 / baja tahan karat: 0.7 / kuningan: 0.4 / aluminium: 0.4 / tembaga: 0.3
Histeresis	[X01]	1...15
Deviasi titik peralihan	[X01]	-10...10
Kondisi pengoperasian		
Suhu sekitar	[°C]	-25...80
Perlindungan		IP 67
Pengujian/persetujuan		
EME	EN 60947-5-2	
Data teknis		
Casing		persegi panjang
Pemasangan		non-flush mountable
Dimensi	[mm]	60 x 36 x 10
Material		PBT
Elemen display/pengoperasian		
Display	status peralihan	1 x LED, kuning
Keterangan		
Jumlah paket		1 buah
Koneksi listrik		
Kabel: 2 m, PUR / PVC; 2 x 0.14 mm²		
Koneksi		



BN = Warna core :
 BU = coklat
 biru